## Freestanding Hand Operated Multi-Spray Shower and Hand Operated Eye / Face Wash with 3 Side Panels

**EM660** 

Enware's freestanding multi-spray decontamination showers for use where hazardous substances are used. The multi-sprays ensure maximum coverage of clothing and the highest quality components ensure reliability.

### **KEY FEATURES**

- 16 multi-spray outlets
- · Hand operated multi-spray shower
- · Hand operated eye/ face wash
- Three side panels for enclosed applications
- Stainless steel construction for maximum durability and reliability
- Eye/ face wash serviceable in-situ



### **PRODUCT CODES**

EM660	Freestanding Hand Operated Multi-Spray Shower - 16 Spray and Hand Operated Eye/Face Wash with 3 Side Panels
-------	-------------------------------------------------------------------------------------------------------------------


Version: Feb 22




# Freestanding Hand Operated Multi-Spray Shower and Hand Operated Eye / Face Wash with 3 Side Panels

## **TECHNICAL INFORMATION**

Decontamination Shower		
Inlet Connection	25mm (1" BSP) Female	
	NPT and flange connections available for petro-chemical and offshore applications	
Flow Rates	97 lpm @ 200 kPa 118 lpm @ 300 kPa 153 lpm @ 500 kPa 216 lpm @ 1000 kPa	
Eye/Face Wash		
Inlet Connection	1/2" BSP male (DN 15mm) with olive compression fitting	
Water Supply Line Size	Supply piping shall be adequately sized to meet flow requirements	
Minimum Requirements	Min Working Pressure: 210 kPa	
and AS/NZS 4775 compliance	Caution should be taken when pressure exceeds 550 kPa	
	Minimum Flow 11.4 lpm	
Enware Performance	At Working Pressure: 210 kPa	
	Eye/Face Wash Flow 26 lpm	
Waste Water Outlet Connection	G 1-1/2" BSP	







Installation of eye/face wash equipment shall be in accordance with AS/NZS4775 or ANSI Standard Z358.1 - whichever is applicable to the installation.

## Enware Australia advises:

1. Due to ongoing Research and Development, specifications may change without notice. 2. Component specifications may change on some export models. 3. Refer to warranty statement for warranty details - www.enware.com.au/warranty

Version: Feb 22

